



TL-D Standard Colours 標準顏色日光燈 系列

TL-D 15W/54-765 1SL/50

低壓水銀放電燈管，配備直徑 26 mm 的套管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
壽命 (故障率 50%) (標稱)	13,000 h
照明技術	
色碼	54-765
光通量	725 lm
色彩名稱	冷日光色
相關色彩溫度 (規範)	6200 K
演色性指數 (CRI)	72
運轉與電力	
耗電量	15.0 W
燈具電流 (標稱)	0.310 A
電壓 (標稱)	51 V


電壓 (標稱)	51 V
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T8 [26 mm (T8)]
認證與應用	
汞 (Hg) 含量 (標稱)	8.0 mg
能源消耗 kWh/1000 h	20 kWh
產品資料	
下訂產品名稱	TL-D 15W/54-765 1SL/50
完整產品名稱	TL-D 15W/54-765 1SL/50
完整產品代碼	871150072221865

TL-D Standard Colours 標準顏色日光燈系列

訂單代碼	928024805436
材質 Nr. (12NC)	928024805436
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500722218


分子 - 每一外盒包裝	50
EAN/UPC - 箱	8711500641328

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 15W/54-765 1SL/50	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

光度数据




Spectral Power Distribution Colour - TL-D 15W/54-765 1SL/50

壽命




Life Expectancy Diagram - TL-D 15W/54-765 1SL/50



Life Expectancy Diagram - TL-D 15W/54-765 1SL/50

TL-D Standard Colours 標準顏色日光燈系列

壽命



Lumen Maintenance Diagram - TL-D 15W/54-765 1SL/50

