



# TL-D Standard Colours

## TL-D 15W/54-765 1SL/50

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	725 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	15.0 W
Lamp Current (Nom)	0.310 A
Voltage (Nom)	51 V
Voltage (Nom)	51 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	20 kWh
Product Data	
Order product name	TL-D 15W/54-765 1SL/50
Full product name	TL-D 15W/54-765 1SL/50
Full product code	871150072221865
Order code	928024805436
Material Nr. (12NC)	928024805436
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500722218

TL-D Standard Colours


Numerator - Packs per outer box	50
EAN/UPC - Case	8711500641328

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 15W/54-765 1SL/50	28 mm	437.4 mm	444.5 mm	442.1 mm	451.6 mm

Photometric data




Spectral Power Distribution Colour - TL-D 15W/54-765 1SL/50

Lifetime



Life Expectancy Diagram - TL-D 15W/54-765 1SL/50



Life Expectancy Diagram - TL-D 15W/54-765 1SL/50

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 15W/54-765 1SL/50

