



# TL-D Blacklight Blue

## TL-D 15W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

| General Information        |                                 |
|----------------------------|---------------------------------|
| Cap-Base                   | G13 [Medium Bi-Pin Fluorescent] |
| Life to 50% Failures (Nom) | 8,000 hour(s)                   |
| Useful Life (Nom)          | 5,000 hour(s)                   |
| Light Technical            |                                 |
| Color Code                 | 108 [08 lead free glass]        |
| Color Designation          | Blacklight Blue                 |
| Operating and Electrical   |                                 |
| Power Consumption          | 15.9 W                          |
| Lamp Current (Nom)         | 0.310 A                         |
| Voltage (Nom)              | 54 V                            |
| Voltage (Nom)              | 54 V                            |
| Mechanical and Housing     |                                 |
| Bulb Shape                 | T26 [T 26mm]                    |

| Approval and Application        |                     |
|---------------------------------|---------------------|
| Mercury (Hg) Content (Nom)      | 5.0 mg              |
| UV                              |                     |
| UV-A Radiation 100Hr (IEC)      | 3.0 W               |
| Product Data                    |                     |
| Full product code               | 871150095109040     |
| Order product name              | TL-D 15W BLB 1SL/25 |
| Order code                      | 928024810803        |
| Numerator - Quantity Per Pack   | 1                   |
| Numerator - Packs per outer box | 25                  |
| Material Nr. (12NC)             | 928024810803        |
| Full product name               | TL-D 15W BLB 1SL/25 |
| EAN/UPC - Case                  | 8711500951106       |
| EAN/UPC - Product/Case          | 8711500951090       |


# TL-D Blacklight Blue

## Dimensional drawing



| Product             | D (max) | A (max)  | B (max)  | B (min)  | C (max)  |
|---------------------|---------|----------|----------|----------|----------|
| TL-D 15W BLB 1SL/25 | 28 mm   | 437.4 mm | 444.5 mm | 442.1 mm | 451.6 mm |

## Photometric data



Spectral Power Distribution Colour - TL-D 15W BLB 1SL/25

