



# TL-D Standard Colours

## TLD 30W STANDARD 25PCS

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h

Light Technical	
Color Code	75
Luminous Flux (Nom)	1310 lm
Color Designation	Daylight
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	83 %
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	70

Operating and Electrical	
Power (Nom)	30 W
Lamp Current (Nom)	0.360 A
Voltage (Nom)	98 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg


  

Product Data	
Full product code	872790091804500
Order product name	TLD 30W STANDARD 25PCS
EAN/UPC - Product	8727900918045
Order code	928025407548
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928025407548
Net Weight (Piece)	108.600 g

### Warnings and Safety

## TL-D Standard Colours

### Dimensional drawing



#### Product

TLD 30W STANDARD 25PCS

TL-D 30W/75

