



TL-E LIFEMAX

Standard Colours JIS

TL-E 30W/54 JIS 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important. The lamp complies with the Japanese Industrial Standard.

Product data

General Information	
Cap-Base	G10Q [G10q]
Life to 50% Failures (Nom)	13000 h
Light Technical	
Color Code	54
Luminous Flux (Nom)	1410 lm
Color Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	75 %
Lumen Maintenance 5000 h (Nom)	66 %
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	47 lm/W
Color Rendering Index (Nom)	75
Operating and Electrical	
Power (Nom)	28.0 W
Lamp Current (Nom)	0.600 A
Voltage (Nom)	55 V
Controls and Dimming	
Dimmable	No
Product Data	
Full product code	871150064034502
Order product name	TL-E 30W/54 JIS 1CT/20
EAN/UPC - Product	8711500640345
Order code	928026105436
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	928026105436
Net Weight (Piece)	0.130 kg

TL-E LIFEMAX Standard Colours JIS

Dimensional drawing

F

Product	E (min)	E (max)	l (min)	l (max)
TL-E 30W/54 JIS 1CT/20	220.5 mm	225.5 mm	163.5 mm	167 mm

TL-E 30W/54 JIS

