



Actinic BL TL-E

Actinic BL TL-E 22W/10 1CT/20

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

产品数据


基本資訊	
接口	G10Q [G10q]
主要應用	Insect traps
至 50% 故障的使用時間 (標稱)	9000 h
可用使用時間 (標稱)	4000 h
照明科技	
色碼	10
色彩名稱	Ultra Violet A
500 小時後的流明衰減	15 %
500 小時後的流明衰減	25 %
運作和電氣	
Power (Rated) (Nom)	22 W
燈具電流 (標稱)	0.4 A
電壓 (標稱)	62 V
應用	
汞 (Hg) 含量 (標稱)	8 mg

紫外線	
UV-B/UV-A (IEC)	0.1 %
UV-A 輻射 100Hr (IEC)	3.9 W
產品參數	
完整產品碼	871150028513305
訂購產品名稱	Actinic BL TL-E 22W/10 1CT/20
EAN/UPC - 產品	8711500285133
訂購代碼	928026201005
分子 - 各件數量	1
分子 - 每一外盒內件數	20
材質編號(12NC)	928026201005
淨重 (件)	0.110 kg

Actinic BL TL-E

安全提示



二维绘图



Product	D (max)	D (min)	F (max)	F (min)	E (min)	E (max)
Actinic BL TL-E 22W/10 1CT/20	30.9 mm	26.2 mm	155.6 mm	149.1 mm	205.0 mm	213.5 mm

TL-E 22W/10

光度数据



XDPO_XURTLE_10-Spectral power distribution Colour

