



TL-E Circular Standard Colours

TL-E 32W/54-765 1CT/12

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G10q
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54-765
Luminous Flux	1,750 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Luminous Efficacy (rated) (Nom)	57 lm/W
Color rendering index (CRI)	72
Operating and Electrical	
Power Consumption	32.0 W
Lamp Current (Nom)	0.450 A
Voltage (Nom)	81 V


Voltage (Nom)	81 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T29
Approval and Application	
Mercury (Hg) Content (Nom)	9 mg
Product Data	
Order product name	TL-E 32W/54-765 1CT/12
Full product name	TL-E 32W/54-765 1CT/12
Full product code	871150063387315
Order code	928026305460
Material Nr. (12NC)	928026305460

TL-E Circular Standard Colours

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500633873
Numerator - Packs per outer box	12


EAN/UPC - Case	8711500559388
----------------	---------------

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/54-765 1CT/12	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

Photometric data



Spectral Power Distribution Colour - TL-E 32W/54-765 1CT/12

