



MASTER TL-E Circular Super 80

TL-E 32W/840 1CT/4

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	G10q	81 V	
Nominal lifetime	15,000 h	Voltage (Nom)	
Life to 50% Failures (Nom)	13,000 h	81 V	
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	
Luminous Flux	2,375 lm	Yes	
Color Designation	Cool White (CW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	4000 K	Bulb Shape	
Luminous Efficacy (rated) (Nom)	74 lm/W	C-T29	
Color rendering index (CRI)	80	Approval and Application	
Operating and Electrical		Mercury (Hg) Content (Nom)	
Power Consumption	32.0 W	8 mg	
Lamp Current (Nom)	0.450 A	Energy Consumption kWh/1000 h	
		35 kWh	
		Product Data	
		Order product name	
		TL-E 32W/840 1CT/4	
		Full product name	
		TL-E 32W/840 1CT/4	

MASTER TL-E Circular Super 80

Full product code	871150055968501
Local code description	TLE32W840
Order code	928026384040
Material Nr. (12NC)	928026384040
Local order code	TLE32W840
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500559685
Numerator - Packs per outer box	4
EAN/UPC - Case	8711500288820

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/840 1CT/4	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

Photometric data



Spectral Power Distribution Colour - TL-E 32W/840 1CT/4

