



# MASTER TL-E Circular Super 80

## TL-E 32W/865 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Product data

General Information		LLMF 8000 h Rated	
Cap base	G10Q [ G10q]		73 %
Life to 50% failures (nom.)	13000 h	<b>Operating and Electrical</b>	
LSF 2000 h Rated	98 %	Power (Rated) (Nom)	32.0 W
LSF 4000 h Rated	77 %	Lamp current (nom.)	0.450 A
LSF 6000 h Rated	60 %	Voltage (Nom)	81 V
LSF 8000 h Rated	45 %	<b>Temperature</b>	
<b>Light Technical</b>		Design temperature (nom.)	25 °C
Colour Code	865 [ CCT of 6,500 K]	<b>Controls and Dimming</b>	
Lamp Luminous Flux 25°C EL (Nom)	2310 lm	Dimmable	yes
Lamp Luminous Flux (Nom)	2310 lm	<b>Approval and Application</b>	
Colour Designation	Cool Daylight	Energy efficiency label (EEL)	A
Colour Temperature, horizontal (Nom)	6500 K	Mercury (Hg) content (nom.)	8 mg
Lamp Luminous Efficacy EM (Nom)	72 lm/W	Energy Consumption kWh/1000 h	35 kWh
Colour Rendering Index, horiz (Nom)	80	<b>Product Data</b>	
LLMF 2000 h Rated	84 %	Full product code	871150064038300
LLMF 4000 h Rated	79 %		
LLMF 6000 h Rated	75 %		


# MASTER TL-E Circular Super 80

Order product name	TL-E 32W/865 1CT/20
EAN/UPC – product	8711500640383
Order code	928026386574
Numerator – quantity per pack	1
Numerator – packs per outer box	20

Material no. (12NC)	928026386574
Net weight (piece)	0.110 kg
ILCOS Code	FSC-32/65/1B-E-G10q-29/299

## Warnings and Safety

## Dimensional drawing



TL-E 32W/865

## Product

TL-E 32W/865 1CT/20

