



# MASTER TL-E Circular Super 80

## TL-E 32W/865 1CT/20

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


<b>General Information</b>		<b>Voltage (Nom)</b>		81 V
Cap-Base	G10q	<b>Voltage (Nom)</b>		81 V
Nominal lifetime	8,000 h			
Life to 50% Failures (Nom)	13,000 h	<b>Controls and Dimming</b>		
		Dimmable		Yes
<b>Light Technical</b>		<b>Mechanical and Housing</b>		
Color Code	865 [CCT of 6500K]	Bulb Shape		C-T29
Luminous Flux	2,310 lm	<b>Approval and Application</b>		
Color Designation	Cool Daylight	Mercury (Hg) Content (Nom)		8 mg
Correlated Color Temperature (Nom)	6500 K	Energy Consumption kWh/1000 h		35 kWh
Luminous Efficacy (rated) (Nom)	72 lm/W	<b>Product Data</b>		
Color rendering index (CRI)	80	Order product name		TL-E 32W/865 1CT/20
<b>Operating and Electrical</b>		Full product name		TL-E 32W/865 1CT/20
Power Consumption	32.0 W			
Lamp Current (Nom)	0.450 A			

# MASTER TL-E Circular Super 80

Full product code	871150064038300
Local code description	TLE32W865
Order code	928026386574
Material Nr. (12NC)	928026386574
Local order code	TLE32W865
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711500640383
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813616

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 32W/865 1CT/20	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

