



# Circline

## FC8T9/COOL WHITE PLUS

T9 4-Pin Circular Fluorescent Lamps.

### Product data


General Information	
Base	G10Q [ G10q]
Life to 50% Failures (Nom)	13000 h
Light Technical	
Color Code	33
Initial lumen (Nom)	1050 lm
Color Designation	Cool White (CW)
Lumen Maintenance 2000 h (Nom)	80 %
Lumen Maintenance 5000 h (Nom)	71 %
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	62
Operating and Electrical	
Power (Rated) (Nom)	20.5 W
Lamp Current (Nom)	0.37 A
Voltage (Nom)	61 V

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	FC8T9/COOL WHITE PLUS
EAN/UPC - Product	046677391164
Order code	391169
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928028403335
Net Weight (Piece)	0.110 kg

### Warnings and Safety

# Circline

## Dimensional drawing



### Product

FC8T9/COOL WHITE PLUS

TL-E 22W/33 RS

