



Circline

FC8T9/SOFT WHITE/22W/8 12 PK

T9 4-Pin Circular Fluorescent Lamps.

Product data


General Information	
Base	G10Q [G10q]
Life to 50% Failures (Nom)	13000 h
Light Technical	
Color Code	830 [CCT of 3000K]
Initial lumen (Nom)	1150 lm
Color Designation	Soft White
Lumen Maintenance 2000 h (Nom)	80 %
Lumen Maintenance 5000 h (Nom)	72 %
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	80
Operating and Electrical	
Power (Rated) (Nom)	20.5 W
Lamp Current (Nom)	0.37 A
Voltage (Nom)	61 V

Controls and Dimming	
Dimmable	No
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
XUCDM.COPY.Product.Title	FC8T9/SOFT WHITE/22W/8 12 PK
EAN/UPC - Product	046677392222
Order code	392225
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928028483035
Net Weight (Piece)	0.110 kg

Warnings and Safety

Circline

Dimensional drawing



TL-E 22W/830 RS

Product

FC8T9/SOFT WHITE/22W/8 12 PK

