



Circline

FC12T9/DAYLIGHT DELUXE 12PK

T9 4-Pin Circular Fluorescent Lamps.

Warnings and Safety


- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G10Q [G10q]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54
Luminous Flux	1,570 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	31 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	84 V
Voltage (Nom)	84 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	C-T29
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	FC12T9/DAYLIGHT DELUXE 12PK
Full product name	FC12T9/DAYLIGHT DELUXE 12PK
Order code	262600
Material Nr. (12NC)	928028605435
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677262600
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677262605

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
FC12T9/ DAYLIGHT DELUXE 12PK	1-1/4 inch	1-1/16 inch	11-1/2 inch	12 inch	9-7/16 inch	9-11/16 inch

