



# Circline

## FC12T9/SOFTWHITE/32W/12 12PK

T9 4-Pin Circular Fluorescent Lamps.

### Product data

General Information	
Base	G10Q [ G10q]
Life to 50% Failures (Nom)	13000 h

Light Technical	
Color Code	830 [ CCT of 3000K]
Initial lumen (Nom)	1900 lm
Color Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	84 %
Lumen Maintenance 5000 h (Nom)	77 %
Correlated Color Temperature (Nom)	3000 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	31 W
Lamp Current (Nom)	0.43 A

Voltage (Nom)	84 V
---------------	------

Controls and Dimming	
Dimmable	No


  

Product Data	
Order product name	FC12T9/SOFTWHITE/32W/12 12PK
EAN/UPC - Product	046677391225
Order code	391227
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	928028683035
Net Weight (Piece)	0.180 kg

### Warnings and Safety

# Circline

## Dimensional drawing



TL-E 32W/830 RS

### Product

FC12T9/SOFTWHITE/32W/12 12PK

