



# Circline

## FC12T9/SOFTWHITE/32W/12 12PK

T9 4-Pin Circular Fluorescent Lamps.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General Information	
Cap-Base	G10Q [G10q]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,900 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	85
Operating and Electrical	
Power Consumption	31 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	84 V
Voltage (Nom)	84 V

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	C-T29
Product Data	
Order product name	FC12T9/SOFTWHITE/32W/12 12PK
Full product name	FC12T9/SOFTWHITE/32W/12 12PK
Order code	391227
Material Nr. (12NC)	928028683035
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677391225
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677391220

# Circline

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
FC12T9/	1-1/4 inch	1-1/16	11-1/2	12 inch	9-7/16	9-11/16
SOFTWHITE/32W/1		inch	inch		inch	inch
2 12PK						

