



# TL-M Rapid Start Standard Colours

## TL-M RS 40W/33-640 SLV/25

The TL-M RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating and an external ignition strip. It is suitable for situations where low temperatures and high humidity require fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	39.5 W
Life to 50% Failures (Nom)	13,000 hour(s)	Lamp Current (Nom)	0.430 A
<b>Light Technical</b>		Voltage (Nom)	101 V
Color Code	33-640	Voltage (Nom)	101 V
Luminous Flux	2,850 lm	<b>Controls and Dimming</b>	
Color Designation	Cool White (CW)	Dimmable	Yes
Correlated Color Temperature (Nom)	4100 K	<b>Mechanical and Housing</b>	
Luminous Efficacy (rated) (Nom)	72 lm/W	Bulb Shape	T12 [38 mm (T12)]
Color rendering index (CRI)	63		

# TL-M Rapid Start Standard Colours

## Approval and Application


Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	47 kWh

## Product Data

Order product name	TL-M RS 40W/33-640 SLV/25
Full product name	TL-M RS 40W/33-640 SLV/25
Full product code	871150072429840


Order code	928030503371
Material Nr. (12NC)	928030503371
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500724298
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500724304

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS 40W/33-640 SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

## Photometric data



Spectral Power Distribution Colour - TL-M RS 40W/33-640 SLV/25

