



# TL-M Rapid Start Standard Colours

## TL-M RS 65W/33-640 1SL/25

The TL-M RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicon coating and an external ignition strip. It is suitable for situations where low temperatures and high humidity require fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	33-640
Luminous Flux	4,750 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	74 lm/W
Color rendering index (CRI)	63
Operating and Electrical	
Power Consumption	64.0 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	110 V

Voltage (Nom)	110 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12 [38 mm (T12)]
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	74 kWh
Product Data	
Order product name	TL-M RS 65W/33-640 1SL/25
Full product name	TL-M RS 65W/33-640 1SL/25
Full product code	871150072486140


TL-M Rapid Start Standard Colours

Order code	928031003371
Material Nr. (12NC)	928031003371
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500724861


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500724878

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS 65W/33-640 1SL/25	40.5 mm	1,500 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm



Photometric data



Spectral Power Distribution Colour - TL-M RS 65W/33-640 1SL/25

