



# TL-X XL

## TL-X XL 20W/33-640 SLV/25

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

### Product data


General Information	
Cap base	FA6 [ FA6]
Life to 10% failures (nom.)	21000 h
Life to 50% failures (nom.)	26000 h
Light Technical	
Colour Code	33-640
Lamp Luminous Flux 25°C EL (Nom)	940 lm
Colour Designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	0 %
Lumen maintenance 2,000 hours (nom.)	88 %
Lumen maintenance 5,000 hours (nom.)	83 %
Colour Temperature, horizontal (Nom)	4100 K
Lamp Luminous Efficacy EM (Nom)	47 lm/W
Colour Rendering Index, horiz (Nom)	63
Operating and Electrical	
Power (Rated) (Nom)	20.0 W
Lamp current (nom.)	0.380 A
Voltage (Nom)	58 V

Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	12.0 mg
Energy Consumption kWh/1000 h	25 kWh
Product Data	
Full product code	871150026135940
Order product name	TL-X XL 20W/33-640 SLV/25
EAN/UPC – product	8711500261359
Order code	928037703332
Local Code	TLXXL20W33
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928037703332
Net weight (piece)	124.000 g
ILCOS Code	FD-20/41/2B-LC/N-Fa6

### Warnings and Safety

# TL-X XL


## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 20W/33-640 SLV/25	40.5 mm	574 mm	592.5 mm	589 mm	611 mm

TL-X XL 20W/33-640

## Photometric data



Lightcolour /33-640

Lightcolour /33-640

