



Ecopassport

TL-X XL

TL-X XL 40W/33-640 SLV/25



Energy

- Power (Rated) (Nom) : 39.0 W
- Luminous Efficacy (rated) (Nom) : 58 lm/W
- Energy Efficiency Label (EEL) : B
- Dimmable : Yes



Substances

- Mercury (Hg) Content (Nom) : 12.0 mg



lifetime

- Life To 10% Failures (Nom) : 21000 h
- Life to 50% Failures (Nom) : 26000 h

[field not found 'specificationOverviewText_title']

Our environmental product specifications overview

At Philips, we strive to make the world healthier and more sustainable through innovation. Our sustainability efforts are globally recognized and reflected e.g., by our continuous leading positions global rankings like the Dow Jones Sustainability Index and the Carbon Disclosure Project. In our eco-design process we focus on Energy, Weight, Recycling, Packaging, Substances, and Reliability to view and further

PHILIPS

2018, August 11
data subject to change
Order code : 928037903332