



TL-X XL 日光燈管

TL-X XL 40W/33-640 SLV/25

直徑 38 mm 的單接腳螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊	
燈座基底	FA6 [FA6]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	26,000 h
照明技術	
色碼	33-640
光通量	2,300 lm
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	0.38
色度坐標 Y (Nom)	0.38
相關色彩溫度 (規範)	4000 K
光效 (額定) (標準)	58 lm/W
演色性指數 (CRI)	60
運轉與電力	
耗電量	40.0 W
燈具電流 (標稱)	0.430 A
電壓 (標稱)	103 V
電壓 (標稱)	103 V

控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T12 [38 mm (T12)]
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	12 mg
汞 (Hg) 含量 (標稱)	12.0 mg
能源消耗 kWh/1000 h	40 kWh
EPREL 註冊碼	423515
產品資料	
下訂產品名稱	TL-X XL 40W/33-640 SLV/25
完整產品名稱	TL-X XL 40W/33-640 SLV/25
完整產品代碼	871150026137340
訂單代碼	928037903332
材質 Nr. (12NC)	928037903332
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500261373

TL-X XL 日光燈管


分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500261380

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 40W/33-640 SLV/25	40.5 mm	1,183.5 mm	1,202 mm	1,198.5 mm	1,220.5 mm

光度数据



Spectral Power Distribution Colour - TL-X XL 40W/33-640 SLV/25

