



TL-X XL

TL-X XL 40W/33-640 SLV/25

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	FA6
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	26,000 h
Light Technical	
Color Code	33-640
Luminous Flux	2,300 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	58 lm/W
Color rendering index (CRI)	60
Operating and Electrical	
Power Consumption	40.0 W
Lamp Current (Nom)	0.430 A
Voltage (Nom)	103 V
Voltage (Nom)	103 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T12
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	12 mg
Mercury (Hg) Content (Nom)	12.0 mg
Energy Consumption kWh/1000 h	40 kWh
EPREL Registration Number	423515
Product Data	
Order product name	TL-X XL 40W/33-640 SLV/25
Full product name	TL-X XL 40W/33-640 SLV/25
Full product code	871150026137340
Local code description	TLXXL40W33
Order code	928037903332
Material Nr. (12NC)	928037903332
Local order code	TLXXL40W33

TL-X XL

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500261373
Numerator - Packs per outer box	25


EAN/UPC - Case	8711500261380
----------------	---------------

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-X XL 40W/33-640 SLV/25	40.5 mm	1,183.5 mm	1,202 mm	1,198.5 mm	1,220.5 mm

Photometric data



Spectral Power Distribution Colour - TL-X XL 40W/33-640 SLV/25

