



# TL-D U

## TL-D U 18W/840 SLV 24

This fluorescent lamp with a U-shaped tube enables the creation of compact luminaires. Often used for sign lighting and residential lighting, e.g. in post-top lanterns.


### Product data

General Information	
Cap-Base	2G13 [ 2G13]
Life to 50% Failures (Nom)	7500 h
LSF 2000 h Rated	98 %
LSF 4000 h Rated	93 %
LSF 6000 h Rated	72 %
LSF 8000 h Rated	40 %
Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	1350 lm
Luminous Flux (Rated) (Nom)	1350 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Rendering Index (Nom)	85
LLMF 2000 h Rated	85 %
LLMF 4000 h Rated	78 %
LLMF 6000 h Rated	71 %
LLMF 8000 h Rated	65 %
Operating and Electrical	
Power (Nom)	18 W
Lamp Current (Nom)	0.370 A

Voltage (Nom)	60 V
Temperature	
Design Temperature (Nom)	25 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	7 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Full product code	872790086004700
Order product name	TL-D U 18W/840 SLV 24
EAN/UPC - Product	8727900860047
Order code	928038484002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24
Material Nr. (12NC)	928038484002
Net Weight (Piece)	136.000 g
ILCOS Code	FDU-18/40/1B-E-2G13

Warnings and Safety


Dimensional drawing




TL-D U 18W/840

<b>Product</b>
TL-D U 18W/840 SLV 24

Photometric data



LDPB\_TL-D-U\_840-Spectral power distribution B/W



LDPO\_TL-D-U\_840-Spectral power distribution Colour

