



TUV T8

TUV 30W 1SL/25-Latest

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer almost constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

产品数据


一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
可用使用始間 (標稱)	9,000 h
照明技術	
色碼	TUV
色彩名稱	- [未指定]
使用壽命期間的折舊	15 %
運轉與電力	
耗電量	30 W
燈具電流 (標稱)	0.365 A
電壓 (標稱)	102 V

電壓 (標稱)	102 V
機械與外罩	
燈泡形狀	T26 [T 26mm]
認證與應用	
汞 (Hg) 含量 (標稱)	2.0 mg
UV	
UV-C 輻射 (100 小時)	12.3 W
產品資料	
下訂產品名稱	TUV 30W 1SL/25-Latest
完整產品名稱	TUV 30W 1SL/25-Latest

完整產品代碼	871150072620940
訂單代碼	928039504005
材質 Nr. (12NC)	928039504005
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500726209


分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500638625

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 30W 1SL/25-Latest	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm

光度数据



Spectral Power Distribution Colour - TUV 30W 1SL/25-Latest

