



MASTER TL-D 90 Graphica



MASTER TL-D 90 Graphica 18W/965 SLV/10

This TL-D lamp has excellent color rendering which makes it very suitable for the graphical and printing industry to check the quality of printed material.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Lamp Current (Nom) | 0.360 A |
|------------------------------------|---------------------------------|-------------------------------|--|
| Cap-Base | G13 [Medium Bi-Pin Fluorescent] | Controls and Dimming | |
| Flux measurement reference | Sphere | Dimmable | Yes |
| Life to 50% Failures (Nom) | 8,000 hour(s) | Mechanical and Housing | |
| Light Technical | | Bulb Shape | T8 |
| Color Code | 965 [CCT of 6500K] | Approval and Application | |
| Luminous Flux | 950 lm | Energy Efficiency Class | G |
| Color Designation | Cool Daylight | Mercury (Hg) Content (Nom) | 1.7 mg |
| Chromaticity Coordinate X (Nom) | 0.313 | Energy Consumption kWh/1000 h | 19 kWh |
| Chromaticity Coordinate Y (Nom) | 0.337 | EPREL Registration Number | 423523 |
| Correlated Color Temperature (Nom) | 6500 K | Product Data | |
| Luminous Efficacy (rated) (Nom) | 51.6 lm/W | Order product name | MASTER TL-D 90 Graphica 18W/965 SLV/10 |
| Color rendering index (CRI) | 96 | Full product name | MASTER TL-D 90 Graphica 18W/965 SLV/10 |
| Operating and Electrical | | Full product code | 871150088852525 |
| Power Consumption | 18.4 W | | |

MASTER TL-D 90 Graphica

| | |
|-------------------------------|---------------|
| Order code | 928043796581 |
| Material Nr. (12NC) | 928043796581 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500888525 |


| | |
|---------------------------------|---------------|
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 8711500888532 |

Dimensional drawing




| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---|---------|----------|----------|----------|---------|
| MASTER TL-D 90 Graphica 18W/965 SLV/10 | 28 mm | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm |

Photometric data




Spectral Power Distribution Colour - MASTER TL-D 90 Graphica 18W/965 SLV/10

Lifetime




Life Expectancy Diagram - MASTER TL-D 90 Graphica 18W/965 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 Graphica 18W/965 SLV/10

MASTER TL-D 90 Graphica

Lifetime



Lumen Maintenance Diagram - MASTER TL-D 90 Graphica 18W/965 SLV/10

