



MASTER TL-D 90 De Luxe 日光燈管

MASTER TL-D 90 De Luxe 36W/965 SLV/10

直徑 26 mm 的螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	15,000 h
照明技術	
色碼	965 [CCT of 6500K]
光通量	2,850 lm
色彩名稱	冷日光色
色度坐標 X (標稱)	0.313
色度坐標 Y (Nom)	0.337
相關色彩溫度 (規範)	6500 K
光效 (額定) (標準)	77.4 lm/W
演色性指數 (CRI)	93
運轉與電力	
耗電量	36.8 W
燈具電流 (標稱)	0.440 A

控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T8 [26 mm (T8)]
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (標稱)	1.7 mg
能源消耗 kWh/1000 h	37 kWh
EPREL 註冊碼	423526
產品資料	
下訂產品名稱	MASTER TL-D 90 De Luxe 36W/965 SLV/10
完整產品名稱	MASTER TL-D 90 De Luxe 36W/965 SLV/10
完整產品代碼	871150088862425
訂單代碼	928044596581
材質 Nr. (12NC)	928044596581
分子 - 每個包裝的數量	1

MASTER TL-D 90 De Luxe 日光燈管


EAN/UPC - 產品/案例	8711500888624
分子 - 每一外盒包裝	10
EAN/UPC - 箱	8711500888631

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 36W/965 SLV/10	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D 90 De Luxe 36W/965 SLV/10

壽命




Life Expectancy Diagram - MASTER TL-D 90 De Luxe 36W/965 SLV/10



Life Expectancy Diagram - MASTER TL-D 90 De Luxe 36W/965 SLV/10

MASTER TL-D 90 De Luxe 日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL-D 90 De Luxe 36W/965 SLV/10

