



MASTER TL-D 90 Graphica

MASTER TL-D 90 Graphica 58W/950 SLV/10

This TL-D lamp has excellent color rendering which makes it very suitable for the graphical and printing industry to check the quality of printed material.

Product data

General Information		LLMF 2000 h Rated	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	LLMF 4000 h Rated	93 %
Life To 10% Failures (Nom)	6000 h	LLMF 6000 h Rated	90 %
Life to 50% Failures (Nom)	8000 h	LLMF 8000 h Rated	88 %
Life to 50% Failures Preheat (Nom)	10000 h	LLMF 12000 h Rated	85 %
LSF 2000 h Rated	99 %	LLMF 16000 h Rated	82 %
LSF 4000 h Rated	99 %	LLMF 20000 h Rated	80 %
LSF 6000 h Rated	99 %		78 %
LSF 8000 h Rated	99 %	Operating and Electrical	
LSF 12000 h Rated	89 %	Power (Nom)	58.5 W
LSF 16000 h Rated	33 %	Lamp Current (Nom)	0.670 A
LSF 20000 h Rated	2 %	Temperature	
		Design Temperature (Nom)	25 °C
		Controls and Dimming	
		Dimmable	Yes
		Approval and Application	
		Energy Efficiency Label (EEL)	B
		Mercury (Hg) Content (Nom)	2 mg
Light Technical			
Color Code	950 [CCT of 5000K]		
Luminous Flux (Nom)	3750 lm		
Luminous Flux (Rated) (Nom)	3750 lm		
Color Designation	Daylight		
Chromaticity Coordinate X (Nom)	348		
Chromaticity Coordinate Y (Nom)	360		
Luminous Efficacy (rated) (Nom)	62.7 lm/W		
Color Rendering Index (Nom)	95		

MASTER TL-D 90 Graphica

Energy Consumption kWh/1000 h	69 kWh
Product Data	
Full product code	871150088875425
Order product name	MASTER TL-D 90 Graphica 58W/950 SLV/10
EAN/UPC - Product	8711500888754
Order code	928045295081

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	928045295081
Net Weight (Piece)	167.000 g
ILCOS Code	FD-58/53/1A-E-G13


Warnings and Safety

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 Graphica 58W/950 SLV/10	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

TL-D Graphica 58W/950

Photometric data



MASTER TL-D 90 Graphica

Lifetime

