

TL-D Colored

TL-D Colored 18W Yellow 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

Product data


General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
Light Technical	
Colour Code	160
Lamp Luminous Flux 25°C EL (Nom)	700 lm
Lamp Luminous Flux (Nom)	700 lm
Colour Designation	Yellow
LLMF 2000 h Rated	85 %
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.360 A
Voltage (Nom)	59 V
Temperature	
Design temperature (nom.)	25 °C

Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	13.0 mg
Energy Consumption kWh/1000 h	23 kWh
Product Data	
Full product code	871150072687240
Order product name	TL-D Colored 18W Yellow 1SL/25
EAN/UPC – product	8711500726872
Order code	928048001605
Local Code	TLD18W16
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048001605
Net weight (piece)	71.000 g

Warnings and Safety

TL-D Colored


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm
Yellow 1SL/25					

TL-D 18W/160 Yellow

Photometric data



LDPB_TL-DCOL_160-Spectral power distribution B/W



Lightcolour TL-D /160

