



# TL-D Colored

## TL-D Colored 18W Yellow 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	160
Luminous Flux	700 lm
Color Designation	Yellow
Operating and Electrical	
Power Consumption	18.0 W
Lamp Current (Nom)	0.360 A
Voltage (Nom)	59 V
Voltage (Nom)	59 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	13.0 mg
Energy Consumption kWh/1000 h	23 kWh
Product Data	
Order product name	TL-D Colored 18W Yellow 1SL/25
Full product name	TL-D Colored 18W Yellow 1SL/25
Full product code	871150072687240
Order code	928048001605
Material Nr. (12NC)	928048001605

TL-D Colored

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500726872
Numerator - Packs per outer box	25


EAN/UPC - Case	8711500726889
----------------	---------------

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 18W Yellow 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

Photometric data



Spectral Power Distribution Colour - TL-D Colored 18W Yellow 1SL/25

