



# TL-D Standard Colours

## TL-D 18W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h

Light Technical	
Color Code	33-640
Initial lumen (Nom)	1200 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	75 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	80 %
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	63

Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp Current (Nom)	0.360 A
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	22 kWh

Product Data	
Order product name	TL-D 18W/33-640 1SL/25
EAN/UPC - Product	8711500950413
Order code	251470
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048003312
Net Weight (Piece)	71.000 g
ILCOS Code	FD-18/41/2B-E-G13

### Warnings and Safety

# TL-D Standard Colours

## Dimensional drawing




TL-D 18W/33-640



### Product

TL-D 18W/33-640 1SL/25

## Photometric data




## Lifetime



LDLE\_TL-DSTD\_0001-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

