



TL-D Standard Colours

TL-D 18W/33-640 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h
Light Technical	
Colour Code	33-640
Lamp Luminous Flux 25°C EL (Nom)	1200 lm
Colour Designation	Cool White (CW)
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Colour Temperature, horizontal (Nom)	4100 K
Colour Rendering Index, horiz (Nom)	63
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.360 A
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Full product code	871150095041340
Order product name	TL-D 18W/33-640 1SL/25
EAN/UPC – product	8711500950413
Order code	95041340
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048003312
Net weight (piece)	71.000 g
ILCOS Code	FD-18/41/2B-E-G13

TL-D Standard Colours

Dimensional drawing




TL-D 18W/33-640

Product

TL-D 18W/33-640 1SL/25


Photometric data




Lightcolour /33-640

Lightcolour /33-640

Lifetime




LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

