



# TL-D Standard Colours

## TL-D 18W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

Light Technical	
Colour Code	54-765
Lamp Luminous Flux 25°C EL (Nom)	1050 lm
Colour Designation	Cool Daylight
Lumen maintenance 10,000 hours (nom.)	75 %
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	80 %
Colour Temperature, horizontal (Nom)	6200 K
Colour Rendering Index,horiz (Nom)	72

Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.360 A
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8.0 mg
Energy Consumption kWh/1000 h	22 kWh

Product Data	
Full product code	871150095043740
Order product name	TL-D 18W/54-765 1SL/25
EAN/UPC – product	8711500950437
Order code	95043740
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048005422
Net weight (piece)	71.000 g
ILCOS Code	FD-18/62/2A-E-G13

# TL-D Standard Colours

## Dimensional drawing




TL-D 18W/54-765


### Product

TL-D 18W/54-765 1SL/25

## Photometric data




Lightcolour /54-765




Lightcolour /54-765

## Lifetime




LDLE\_TL-DSTD\_0001-Life expectancy diagram



LDLE\_TL-DSTD\_0002-Life expectancy diagram

## TL-D Standard Colours

### Lifetime



LDLM\_TL-DSTD\_0001-Lumen maintenance diagram

