



TL-D Blacklight Blue

TL-D 18W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
壽命 (故障率 50%) (標稱)	13,000 h
可用使用始間 (標稱)	5,000 h
照明技術	
色碼	108 [08 lead free glass]
色彩名稱	黑光藍色
運轉與電力	
耗電量	18 W
燈具電流 (標稱)	0.36 A
電壓 (標稱)	59 V
電壓 (標稱)	59 V
機械與外罩	
燈泡形狀	T26 [T 26mm]

認證與應用	
汞 (Hg) 含量 (標稱)	5.0 mg
UV	
UV-A 輻射 100Hr (IEC)	3.9 W
產品資料	
下訂產品名稱	TL-D 18W BLB 1SL/25
完整產品名稱	TL-D 18W BLB 1SL/25
完整產品代碼	871150095111340
訂單代碼	928048010805
材質 Nr. (12NC)	928048010805
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500951113
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500951120


TL-D Blacklight Blue

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W BLB 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

光度数据



Spectral Power Distribution Colour - TL-D 18W BLB 1SL/25

