



# TL-D Snow White

## TL-D 18W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high colour temperature of the Snow White range creates very cool ambience, making the lamp especially suitable in very hot and dry climate conditions.

### Product data

#### General Information

Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

#### Light Technical

Lamp Luminous Flux 25°C EL (Nom)	1000 lm
Colour Designation	Extreme Cool Daylight
Chromaticity coordinate X (nom.)	264
Chromaticity coordinate Y (nom.)	280
Colour Temperature, horizontal (Nom)	12000 K
Colour Rendering Index, horiz (Nom)	75

#### Operating and Electrical

Power (Rated) (Nom)	18 W
Lamp current (nom.)	360 mA
Voltage (Nom)	59 V

#### Approval and Application

Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8 mg
Energy Consumption kWh/1000 h	22 kWh


#### Product Data

Full product code	871150089350540
Order product name	TL-D 18W Snow White 1SL/25
EAN/UPC – product	8711500893505
Order code	89350540
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048045015
Net weight (piece)	71.000 g

### Warnings and Safety

## TL-D Snow White

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W Snow White	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
1SL/25					

