



TL-D Snow White

TL-D 18W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high color temperature of the Snow White range creates very cool ambiances, making the lamp especially suitable in very hot and dry climate conditions.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Luminous Flux	1,000 lm
Color Designation	Extreme Cool Daylight
Chromaticity Coordinate X (Nom)	264
Chromaticity Coordinate Y (Nom)	280
Correlated Color Temperature (Nom)	12000 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	18 W
Lamp Current (Nom)	360 mA
Voltage (Nom)	59 V
Voltage (Nom)	59 V

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Order product name	TL-D 18W Snow White 1SL/25
Full product name	TL-D 18W Snow White 1SL/25
Full product code	871150089350540
Order code	928048045015
Material Nr. (12NC)	928048045015
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500893505
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500893512

TL-D Snow White

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W Snow White 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

