



# TL-D Colored

## TL-D Colored 36W Red 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent ]
Life To 10% Failures (Nom)	12000 h
Life to 50% Failures (Nom)	15000 h
Light Technical	
Color Code	150
Luminous Flux (Nom)	55 lm
Luminous Flux (Rated) (Nom)	55 lm
Color Designation	Red (HO)
LLMF 2000 h Rated	85 %
Operating and Electrical	
Power (Nom)	36.0 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V
Temperature	
Design Temperature (Nom)	25 °C

### Warnings and Safety

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	E
Mercury (Hg) Content (Nom)	13.0 mg
Energy Consumption kWh/1000 h	51 kWh
Product Data	
Full product code	871150072748040
Order product name	TL-D Colored 36W Red 1SL/25
EAN/UPC - Product	8711500727480
Order code	928048501505
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048501505
Net Weight (Piece)	135.000 g

# TL-D Colored

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 36W Red	28.0 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
1SL/25					

TL-D 36W/150 Red

## Photometric data

