



TL-D Colored

TL-D Colored 36W Yellow 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15,000 h		
Light Technical		Mechanical and Housing	
Color Code	160	Bulb Shape	T8
Luminous Flux	1,580 lm		
Color Designation	Yellow	Approval and Application	
		Mercury (Hg) Content (Nom)	13.0 mg
		Energy Consumption kWh/1000 h	44 kWh
Operating and Electrical		Product Data	
Power Consumption	36.0 W	Order product name	TL-D Colored 36W Yellow 1SL/25
Lamp Current (Nom)	0.440 A	Full product name	TL-D Colored 36W Yellow 1SL/25
Voltage (Nom)	103 V	Full product code	871150072751040
Voltage (Nom)	103 V	Local code description	TLD36W16
		Order code	928048501605

TL-D Colored

Material Nr. (12NC)	928048501605
Local order code	TLD36W16
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500727510


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500727527

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 36W Yellow 1SL/25	28.0 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL-D Colored 36W Yellow 1SL/25

