



# TL-D Colored

## TL-D Colored 36W Blue 1SL/25

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

### Product data


General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	12000 h
Life to 50% failures (nom.)	15000 h
Light Technical	
Colour Code	180
Lamp Luminous Flux 25°C EL (Nom)	960 lm
Lamp Luminous Flux (Nom)	960 lm
Colour Designation	Blue (B)
LLMF 2000 h Rated	85 %
Operating and Electrical	
Power (Rated) (Nom)	36.0 W
Lamp current (nom.)	0.440 A
Voltage (Nom)	103 V
Temperature	
Design temperature (nom.)	25 °C

### Warnings and Safety

Controls and Dimming	
Dimmable	yes
Approval and Application	
Energy efficiency label (EEL)	C
Mercury (Hg) content (nom.)	13.0 mg
Energy Consumption kWh/1000 h	45 kWh
Product Data	
Full product code	871150072754140
Order product name	TL-D Colored 36W Blue 1SL/25
EAN/UPC – product	8711500727541
Order code	72754140
Local Code	9280-485-01805
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048501805
Net weight (piece)	135.000 g

## TL-D Colored



### Dimensional drawing



TL-D 36W/180 Blue

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 36W Blue 1SL/25	28.0 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

### Photometric data



Lightcolour TL-D /180

