



# MASTER TL-D Food

## MASTER TL-D Food 36W/79 SLV/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	15,000 h

Light Technical	
Color Code	79
Luminous Flux	1,750 lm
Color Designation	Food
Correlated Color Temperature (Nom)	3800 K
Luminous Efficacy (rated) (Nom)	49 lm/W
Color rendering index (CRI)	74

Operating and Electrical	
Power Consumption	36.0 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T8

Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	43 kWh


  

Product Data	
Order product name	MASTER TL-D Food 36W/79 SLV/25
Full product name	MASTER TL-D Food 36W/79 SLV/25
Full product code	871150070622540
Local code description	TLD36W79
Order code	928048502043
Material Nr. (12NC)	928048502043
Local order code	TLD36W79
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500706225
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500613127


# MASTER TL-D Food

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Food 36W/79 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm




## Photometric data




Spectral Power Distribution Colour - MASTER TL-D Food 36W/79 SLV/25

## Lifetime




Life Expectancy Diagram - MASTER TL-D Food 36W/79 SLV/25



Life Expectancy Diagram - MASTER TL-D Food 36W/79 SLV/25

# MASTER TL-D Food

## Lifetime



Lumen Maintenance Diagram - MASTER TL-D Food 36W/79 SLV/25

