



# MASTER TL-D Food

## MASTER TL-D Food 36W/79 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	15000 h
Life to 50% failures preheat (nom.)	20000 h

Light Technical	
Colour code	79
Luminous flux (nom.)	1750 lm
Colour designation	Food
Lumen maintenance 2,000 hours (nom.)	90 %
Lumen maintenance 5,000 hours (nom.)	85 %
Correlated colour temperature (nom.)	3800 K
Luminous efficacy (rated) (nom.)	49 lm/W
Color rendering index (nom.)	74

Operating and Electrical	
Power (Rated) (Nom)	36.0 W
Lamp current (nom.)	0.440 A
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	yes

Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	5.0 mg
Energy Consumption kWh/1000 h	43 kWh


  

Product Data	
Full product code	871150070622540
Order product name	MASTER TL-D Food 36W/79 SLV/25
EAN/UPC – product	8711500706225
Order code	70622540
Local Code	3679
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048502043
Net weight (piece)	135.000 g
ILCOS Code	FD-36/38/2A-E-G13

### Warnings and Safety

# MASTER TL-D Food

## Dimensional drawing





### Product

MASTER TL-D Food 36W/79 SLV/25

### TL-D Food 36W/79


## Photometric data



### Lightcolour /79

### Lightcolour /79

## Lifetime



### LDLE\_TL-DFOOD\_0002-Life expectancy diagram

# MASTER TL-D Food

## Lifetime

