



TL-D Standard Colours

TL-D 36W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	13,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T8
Luminous Flux	2,850 lm		
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4100 K	Mercury (Hg) Content (Nom)	5.0 mg
Color rendering index (CRI)	63	Energy Consumption kWh/1000 h	43 kWh
Operating and Electrical		Product Data	
Power Consumption	36.0 W	Order product name	TL-D 36W/33-640 1SL/25
Lamp Current (Nom)	0.440 A	Full product name	TL-D 36W/33-640 1SL/25
Voltage (Nom)	103 V	Full product code	871150095045140
Voltage (Nom)	103 V	Order code	928048503312
		Material Nr. (12NC)	928048503312
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500950451

TL-D Standard Colours


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500950468

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W/33-640 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - TL-D 36W/33-640 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 36W/33-640 1SL/25



Life Expectancy Diagram - TL-D 36W/33-640 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 36W/33-640 1SL/25

