



TL-D Standard Colours

TL-D 36W/33-640 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

G13 [Medium Bi-Pin Fluorescent]
13,000 hour(s)
13,000 hour(s)
33-640
2,850 lm
Cool White (CW)
4100 K
63
36.0 W
0.440 A
103 V

Voltage (Nom)	103 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8 [26 mm (T8)]
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	43 kWh
Product Data	
Order product name	TL-D 36W/33-640 1SL/25
Full product name	TL-D 36W/33-640 1SL/25
Full product code	871150070270801


Datasheet, 2023, April 15 data subject to change

TL-D Standard Colours

Order code	928048503382
Material Nr. (12NC)	928048503382
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500702708


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500727657

Dimensional drawing







Photometric data



Spectral Power Distribution Colour - TL-D 36W/33-640 1SL/25

Lifetime






Life Expectancy Diagram - TL-D 36W/33-640 1SL/25

Life Expectancy Diagram - TL-D 36W/33-640 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 36W/33-640 1SL/25

