



TL-D Standard Colours

TL-D 36W/54-765 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h

Light Technical	
Color Code	54-765
Luminous Flux (Nom)	2500 lm
Color Designation	Cool Daylight
Lumen Maintenance 10000 h (Nom)	75 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	80 %
Correlated Color Temperature (Nom)	6200 K
Color Rendering Index (Nom)	72

Operating and Electrical	
Power (Nom)	36.0 W
Lamp Current (Nom)	0.440 A
Voltage (Nom)	103 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	43 kWh

Product Data	
Full product code	692341077032200
Order product name	TL-D 36W/54-765 1SL/25
EAN/UPC - Product	6923410770322
Order code	928048505453
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928048505453
Net Weight (Piece)	0.140 kg
ILCOS Code	FD-36/62/2A-E-G13

Warnings and Safety

TL-D Standard Colours

Dimensional drawing




TL-D 36W/54-765


Product

TL-D 36W/54-765 1SL/25

Photometric data




LDPB_TL-DSTD_54-765-Spectral power distribution B/W




LDPO_TL-DSTD_54-765-Spectral power distribution Colour

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



LDLE_TL-DSTD_0002-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

