



# TL-D Blacklight Blue

## TL-D 36W BLB 1SL/25

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% failures (nom.)	15,000 h
Useful life (nom.)	12,000 h
Light Technical	
Colour Code	108 [08 lead free glass]
Colour designation	Blacklight Blue
Operating and Electrical	
Power Consumption	36 W
Lamp current (nom.)	0.44 A
Voltage (nom.)	103 V
Voltage (nom.)	103 V
Mechanical and Housing	
Bulb shape	T26 [T 26 mm]
Approval and Application	
Mercury (Hg) content (nom.)	5.0 mg

UV	
UV-A radiation 100 hours (IEC)	9.5 W
Product Data	
Order product name	TL-D 36W BLB 1SL/25
Full product name	TL-D 36W BLB 1SL/25
Full EOC	871150095115140
Order code	95115140
Material no. (12 NC)	928048510805
Local order code	3608
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500951151
Numerator – packs per outer box	25
EAN/UPC – Case	8711500951168


TL-D Blacklight Blue

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W BLB 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data



Spectral Power Distribution Colour - TL-D 36W BLB 1SL/25

