



TL-D Snow White

TL-D 36W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high colour temperature of the Snow White range creates very cool ambience, making the lamp especially suitable in very hot and dry climate conditions.

Product data

General Information

Cap base	G13 [Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

Light Technical

Lamp Luminous Flux 25°C EL (Nom)	2370 lm
Colour Designation	Extreme Cool Daylight
Chromaticity coordinate X (nom.)	264
Chromaticity coordinate Y (nom.)	280
Colour Temperature, horizontal (Nom)	12000 K
Colour Rendering Index, horiz (Nom)	75

Operating and Electrical

Power (Rated) (Nom)	36 W
Lamp current (nom.)	440 mA
Voltage (Nom)	103 V

Approval and Application

Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8 mg
Energy Consumption kWh/1000 h	43 kWh


Product Data

Full product code	871150089352940
Order product name	TL-D 36W Snow White 1SL/25
EAN/UPC – product	8711500893529
Order code	89352940
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048545015
Net weight (piece)	135.000 g

Warnings and Safety

TL-D Snow White

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W Snow White 1SL/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

