



TL-D Snow White

TL-D 36W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high color temperature of the Snow White range creates very cool ambiances, making the lamp especially suitable in very hot and dry climate conditions.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Luminous Flux	2,370 lm
Color Designation	Extreme Cool Daylight
Chromaticity Coordinate X (Nom)	264
Chromaticity Coordinate Y (Nom)	280
Correlated Color Temperature (Nom)	12000 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	36 W
Lamp Current (Nom)	440 mA
Voltage (Nom)	103 V
Voltage (Nom)	103 V

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	43 kWh
Product Data	
Order product name	TL-D 36W Snow White 1SL/25
Full product name	TL-D 36W Snow White 1SL/25
Full product code	871150089352940
Order code	928048545015
Material Nr. (12NC)	928048545015
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500893529
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500893536

TL-D Snow White

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 36W Snow White 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

