



TUV T8

TUV 36W SLV/6

TUV T8 lamps are double-ended UVC (germicidal) lamps used in professional water and air disinfection units. TUV T8 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Moreover, they have a long and reliable lifetime, which allows maintenance to be planned for in advance.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Useful life (nom.)	9,000 h
Light Technical	
Colour Code	TUV
Colour designation	- [Not Specified]
Depreciation at useful lifetime	15 %
Operating and Electrical	
Power Consumption	36 W
Lamp current (nom.)	0.44 A
Voltage (nom.)	103 V


Voltage (nom.)	103 V
Mechanical and Housing	
Bulb shape	T26 [T 26 mm]
Approval and Application	
Mercury (Hg) content (nom.)	2.0 mg
UV	
UV-C Radiation at 100 hr	16.4 W
Product Data	
Order product name	TUV 36W SLV/6
Full product name	TUV 36W SLV/6

Full EOC	871150061854210
Order code	61854210
Material no. (12 NC)	928048604003
Local order code	36TUV
SAP numerator – quantity per pack	1

EAN/UPC – Product/Case	8711500618542
Numerator – packs per outer box	6
EAN/UPC – Case	8711500618559

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TUV 36W SLV/6	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm



Photometric data



Spectral Power Distribution Colour – TUV 36W SLV/6

