



TL-D Standard Colours

TL-D 58W/33-640 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h
Light Technical	
Color Code	33-640
Luminous Flux (Nom)	4600 lm
Color Designation	Cool White (CW)
Lumen Maintenance 10000 h (Nom)	75 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	80 %
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	63
Operating and Electrical	
Power (Nom)	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V

Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	68 kWh

Product Data	
Full product code	872790081588700
Order product name	TL-D 58W/33-640 1SL/25
EAN/UPC - Product	8727900815887
Order code	928049003351
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928049003351
Net Weight (Piece)	167.000 g
ILCOS Code	FD-58/41/2B-E-G13

Warnings and Safety

TL-D Standard Colours

Dimensional drawing





TL-D 58W/33-640



Product

TL-D 58W/33-640 1SL/25

Photometric data



Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram

TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

