



TL-D Standard Colours

TL-D 58W/54-765 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)		111 V	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]				
Nominal lifetime	13,000 hour(s)	Controls and Dimming			
Life to 50% Failures (Nom)	13,000 hour(s)	Dimmable	Yes		
Light Technical		Mechanical and Housing			
Color Code	54-765	Bulb Shape	T8 [26 mm (T8)]		
Luminous Flux	4,000 lm	Approval and Application			
Color Designation	Cool Daylight	Mercury (Hg) Content (Nom)	5.0 mg		
Correlated Color Temperature (Nom)	6200 K	Energy Consumption kWh/1000 h	68 kWh		
Color rendering index (CRI)	72	Product Data			
Operating and Electrical		Order product name	TL-D 58W/54-765 1SL/25		
Power Consumption	58.5 W	Full product name	TL-D 58W/54-765 1SL/25		
Lamp Current (Nom)	0.670 A	Full product code	871150070275399		
Voltage (Nom)	111 V				

TL-D Standard Colours

Order code	928049005482
Material Nr. (12NC)	928049005482
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500702753


Numerator - Packs per outer box	25
EAN/UPC - Case	8711500728234

Dimensional drawing





Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54-765 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data



Spectral Power Distribution Colour - TL-D 58W/54-765 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 58W/54-765 1SL/25

Life Expectancy Diagram - TL-D 58W/54-765 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 58W/54-765 1SL/25

