



# TL-D Snow White

## TL-D 58W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high colour temperature of the Snow White range creates very cool ambience, making the lamp especially suitable in very hot and dry climate conditions.

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Life to 10% failures (nom.)	10000 h
Life to 50% failures (nom.)	13000 h

Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	3740 lm
Colour Designation	Extreme Cool Daylight
Chromaticity coordinate X (nom.)	264
Chromaticity coordinate Y (nom.)	280
Colour Temperature, horizontal (Nom)	12000 K
Colour Rendering Index, horiz (Nom)	75

Operating and Electrical	
Power (Rated) (Nom)	58 W
Lamp current (nom.)	670 mA
Voltage (Nom)	111 V

Approval and Application	
Energy efficiency label (EEL)	B
Mercury (Hg) content (nom.)	8 mg
Energy Consumption kWh/1000 h	68 kWh


  

Product Data	
Full product code	871150089354340
Order product name	TL-D 58W Snow White 1SL/25
EAN/UPC – product	8711500893543
Order code	89354340
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928049045015
Net weight (piece)	167.000 g

### Warnings and Safety

## TL-D Snow White

### Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W Snow White 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

