



# TL-D Snow White

## TL-D 58W Snow White 1SL/25

The Snow White is a low-pressure mercury discharge lamp with a tubular 26 mm envelope, available in 18 W, 36 W and 58 W. The extreme high color temperature of the Snow White range creates very cool ambiances, making the lamp especially suitable in very hot and dry climate conditions.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Luminous Flux	3,740 lm
Color Designation	Extreme Cool Daylight
Chromaticity Coordinate X (Nom)	264
Chromaticity Coordinate Y (Nom)	280
Correlated Color Temperature (Nom)	12000 K
Color rendering index (CRI)	75
Operating and Electrical	
Power Consumption	58 W
Lamp Current (Nom)	670 mA
Voltage (Nom)	111 V
Voltage (Nom)	111 V

Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Mercury (Hg) Content (Nom)	5.0 mg
Energy Consumption kWh/1000 h	68 kWh
Product Data	
Order product name	TL-D 58W Snow White 1SL/25
Full product name	TL-D 58W Snow White 1SL/25
Full product code	871150089354340
Order code	928049045015
Material Nr. (12NC)	928049045015
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500893543
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500893550

TL-D Snow White

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W Snow White 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

